



## OPERATION AND CARE MANUAL

### DURGO PRESSURE RELIEF VALVE TYPE SV-55 (4155) DN15/20, DN20/25, DN25/32, DN32/40, DN40/50, DN50/65 BRASS, WITH FKM (FLUOROCARBON RUBBER) WASHER

The Durgo pressure relief valve (PRV) type SV-55 (4155) operates progressively. It is designed to open at the specified set pressure and ensure that the plant is not subjected to a short pressure increase greater than 10%. When the pressure is reduced, the valve will return to being fully closed at the specified opening pressure minus 5%.

The PRV set pressure is fixed in accordance with customer order, and is adjusted to suit the existing installation and pressure used.

The label attached to the valve shows the valve type [Type], year of manufacture and serial number [Year/Id.no.], set pressure [Set pressure], connection [Conn. In/Out], maximum allowable pressure [PS], test pressure [PT], test pressure date [year/month], fluid category [Fluid cat.] and temperature range [Max/Min temp].

#### Applications:

Durgo pressure relief valve (PRV) type SV-55 (4155) in brass, with FKM (fluorocarbon rubber) washer, is intended for use with installations containing air, water or oil. Max temperature 125°C, min temperature -30°C. If the medium contains anything apart from pure air or water, the resistance of the sealing and valve material must be verified, to avoid compromising the sealing / durability of the valve. If there is any uncertainty, please contact Durgo.

#### Maintenance instruction:

Regular function checks must be done on the PRV at least once every 3 months. The valve can be hot, be careful and use protective gloves if necessary. The function check is done by firmly pulling the pressure relief handle and allowing the PRV to blow out medium for about 2 seconds, then release the handle. If the PRV does not open during the function check, it must be exchanged as soon as possible. If the PRV leaks after the function check, this is probably caused by particles which have got stuck between the washer and the sealing surface. Pull the handle again to clear any particles out. The seal must be checked at the same time as the function check. If the seal is broken, the valve must be exchanged. Renovation or service of the PRV must only be done by AB Durgo.

#### Installation:

Valves used for pressure relief during thermal expansion can be installed in any position, since the valve is designed to have its spring housing isolated from the medium.

The PRV valve outlet pipe must be terminated in such a manner that medium which blows out can be discharged without risk of personal injury or property damage.

When installed in a facility where the valve may be exposed to freezing, the valve must be placed or protected so that freezing media can not enter the valve's spring housing.

#### Approval:

Durgo's PRVs are classified as class 4 valves and are CE marked in accordance with AFS 2016:1; Pressure Containing Devices (PED 2014/68/EU).

A EU-declaration of conformity is supplied with all valves.



Id. label





## EU-DECLARATION OF CONFORMITY

DURGO PRESSURE RELIEF VALVE TYPE SV-55 (4155),  
DN15/20, DN20/25, DN25/32, DN32/40, DN40/50, DN50/65  
BRASS, WITH FKM (FLUOROCARBON RUBBER) WASHER

The manufacturer, AB Durgo, hereby certifies that the pressure relief valve complies with the basic safety requirements of the pressure equipment directive 2014/68/EU, converted to Swedish regulations as AFS 2016:1, Pressure containing devices.

Manufacture has taken place through module combination B + D.

The following standards are fully or partly complied with:

SS-EN 12165-CW625N, SS-EN 12164-CW625N, ISO 4126-1,  
SS-EN 10204, SS-EN 1655

EC type approval certificate: PK23-BP-317  
Modul D certificate: K1902534



This EU Declaration of Conformity has been issued on the sole responsibility of the manufacturer.

Solna 1 February 2024

Hans Hansson  
Engineering manager

**Manufacturer:**  
AB Durgo  
Box 3021  
SE-169 03 SOLNA

**Notified body:**  
DEKRA Industrial AB  
Id.nr. 0640  
P.O. Box 1357  
SE-171 26 SOLNA



AB Durgo  
P.O Box 3021  
SE-169 03 SOLNA  
SWEDEN

Phone: +46 8 730 52 80  
e-mail: sales@durgo.se  
www.durgo.se